


Art.-Nr.: 10.01.06.01679



DR 28/21x3 C03 EPDM-15 KE

Teknik veriler

Attribute	Value
Malzeme sertliği [Shore A]	15,0 Shore A
Sızdırmazlık malzemesi	EPDM
Ek fonksiyon alanı tutucu	Bir tarafı yapışkan bant
Yükseklik H	3,00 mm
Dış çap D	28,00 mm
İç çap d	21,00 mm

**Tasarım verileri**

Attribute	Value
Uzunluk L	3,00 mm
Yükseklik H	3,00 mm
Dış çap D	28,00 mm
İç çap d	21,00 mm

Not: DIN ISO 3302-1 M3 uyarınca elastomer parçalar için kabul edilebilir boyut toleransları

Tasarım verileri DR 28/21x3 C03 EPDM-15 KE

**Teknik veriler**

Attribute	Value
Ağırlık	0,13 g

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Sızdırmazlık halkası

DR 28/21x3 C03 EPDM-15 KE



Art.-Nr.: 10.01.06.01679



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.01679



WWW.SCHMALZ.COM/10.01.06.01679