

Art.-Nr.: 10.01.06.01720



DR 60/50x5 S05 EPDM-15 KE

**Технические данные**

| Attribute                                  | Value                         |
|--------------------------------------------|-------------------------------|
| Твердость материала [Shore A]              | 15,0 Shore A                  |
| Материал уплотнения                        | EPDM                          |
| Функция вакуумного захвата большой площади | Клейкая лента с одной стороны |
| Тип материала                              | Губка S, высота 5 мм          |
| Высота H                                   | 5,00 mm                       |
| Наружный диаметр D                         | 60,00 mm                      |
| Внутренний диаметр d                       | 50,00 mm                      |

**Конструктивные данные**

| Attribute            | Value    |
|----------------------|----------|
| Длина L              | 5,00 mm  |
| Высота H             | 5,00 mm  |
| Наружный диаметр D   | 60,00 mm |
| Внутренний диаметр d | 50,00 mm |

Примечание: Допустимые допуски размеров для деталей из эластомера в соответствии с DIN ISO 3302-1 M3

Конструктивные данные DR 60/50x5 S05 EPDM-15 KE

**Технические данные**

| Attribute | Value |
|-----------|-------|
| Вес       | 0,6 g |

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: [www.schmalz.com/10.01.06.01720](http://www.schmalz.com/10.01.06.01720)

[WWW.SCHMALZ.COM/10.01.06.01720](http://WWW.SCHMALZ.COM/10.01.06.01720)