




FG 52 NK-45 N018

## Teknik veriler

| Attribute                  | Value           |
|----------------------------|-----------------|
| Vantuz malzemesi           | Doğal Kauçuk NK |
| Malzeme sertliği [Shore A] | 45,0 Shore A    |
| Boyut                      | 52,00           |
| Körük Sayısı               | 2,5             |



Tasarım verileri FG 52 NK-45 N018

## Tasarım verileri

| Attribute    | Value    |
|--------------|----------|
| Yükseklik H2 | 13,00 mm |
| Yükseklik H  | 48,70 mm |
| Dış çap D1   | 52,0 mm  |
| Kafa çapı Dk | 18,0 mm  |
| d2           | 24,6 mm  |
| İç çap d     | 8,00 mm  |
| Yay stroku Z | 25,0 mm  |
| Çap Ds       | 52,5 mm  |
| Çap Dmax(S)  | 55,0 mm  |

Not: DIN ISO 3302-1 M3 uyarınca elastomer parçalar için kabul edilebilir boyut toleransları

Art.-Nr.: 10.01.06.02382

**Teknik veriler**

| Attribute                          | Value                  |
|------------------------------------|------------------------|
| Meme ucu ailesi                    | N 018                  |
| Vantuz malzemesi                   | Doğal Kauçuk NK        |
| Malzeme sertliği [Shore A]         | 45,0 Shore A           |
| İş parçası yarıçapı dak (dışbükey) | 35,0 mm                |
| Çekme kuvveti                      | 96,00 N                |
| Emme kuvveti (-600mbar)            | 28,52 N                |
| Ağırlık                            | 24,40 g                |
| Cilt                               | 37,587 cm <sup>3</sup> |
| Boyut                              | 52,00                  |
| Körük Sayısı                       | 2,5                    |
| Ürün ailesi                        | FG                     |

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: [www.schmalz.com/10.01.06.02382](http://www.schmalz.com/10.01.06.02382)

[WWW.SCHMALZ.COM/10.01.06.02382](http://WWW.SCHMALZ.COM/10.01.06.02382)