


Art.-Nr.: 10.01.06.02443

**Teknik veriler**

Attribute	Value
Vantuz malzemesi	Yüksek sıcaklık malzemesi HT2
Malzeme sertliği [Shore A]	65.0 Shore A
Boyutlar (LxW)	60 x 30
Bağlantı	G1/4-AG
Meme ucu malzemesi	Alüminyum

SAOB 60x30 HT2-65 G1/4-AG

Çeşitli boyutlarda mevcut olan SAOB HT2 vantuz, elastomer parçaya yapıştırılmış bağlantı nipelini ile birlikte teslim edilir.

**Tasarım verileri**

Attribute	Value
Uzunluk L1	55.70 mm
Genişlik B1	31.00 mm
Yükseklik H	27.00 mm
Nominal çap dn	5.00 mm
Diş G1	G1/4"-M
Diş uzunluğu LG1	8.0 mm
Anahtar boyutu SW1	17.0 mm
Yay stroku Z	7.0 mm
Vantuz genişliği Bs	30.60 mm
Ls	60.60 mm

Tasarım verileri SAOB 60x30 HT2-65 G1/4-AG



Art.-Nr.: 10.01.06.02443

**Teknik veriler**

Attribute	Value
Vantuz malzemesi	Yüksek sıcaklık malzemesi HT2
Malzeme sertliği [Shore A]	65.0 Shore A
Hortum çapı (tavsiye edilen) d	4.0 mm
İş parçası yarıçapı dak (dışbükey)	30.0 mm
Çekme kuvveti	55.00 N
Emme kuvveti (-600mbar)	38.00 N
Ağırlık	44.5 g
Boyutlar (LxW)	60 x 30
Yanal kuvvet	56.0 N
Cilt	10.500 cm ³
Körük Sayısı	1.5
Ürün ailesi	SAOB

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.02443

WWW.SCHMALZ.COM/10.01.06.02443