


**Teknik veriler**

Attribute	Value
Vantuz malzemesi	Yüksek sıcaklık malzemesi HT2
Malzeme sertliği [Shore A]	65.0 Shore A
Boyutlar (LxW)	80 x 40
Bağlantı	G1/4-AG
Meme ucu malzemesi	Alüminyum

SAOB 80x40 HT2-65 G1/4-AG

Çeşitli boyutlarda mevcut olan SAOB HT2 vantuz, elastomer parçaya yapıştırılmış bağlantı nipelini ile birlikte teslim edilir.

**Tasarım verileri**

Attribute	Value
Uzunluk L1	73.30 mm
Genişlik B1	40.00 mm
Yükseklik H	29.70 mm
Nominal çap dn	5.00 mm
Diş G1	G1/4"-M
Diş uzunluğu LG1	8.0 mm
Anahtar boyutu SW1	17.0 mm
Yay stroku Z	9.0 mm
Vantuz genişliği Bs	40.60 mm
Ls	80.60 mm

Tasarım verileri SAOB 80x40 HT2-65 G1/4-AG

Art.-Nr.: 10.01.06.02447

**Teknik veriler**

Attribute	Value
Vantuz malzemesi	Yüksek sıcaklık malzemesi HT2
Malzeme sertliği [Shore A]	65.0 Shore A
Hortum çapı (tavsiye edilen) d	6.0 mm
İş parçası yarıçapı dak (dışbükey)	40.0 mm
Çekme kuvveti	100.00 N
Emme kuvveti (-600mbar)	65.00 N
Ağırlık	57.9 g
Boyutlar (LxW)	80 x 40
Yanal kuvvet	98.0 N
Cilt	21.800 cm ³
Körük Sayısı	1.5
Ürün ailesi	SAOB

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.02447

WWW.SCHMALZ.COM/10.01.06.02447