


Körüklü vantuz (yuvarlak)

FGA 6 NK-45 N004



Art.-Nr.: 10.01.06.02604



FGA 6 NK-45 N004


Teknik veriler

Attribute	Value
Vantuz malzemesi	Doğal Kauçuk NK
Malzeme sertliği [Shore A]	45,0 Shore A
Boyut	6,00
Körük Sayısı	1,5

Tasarım verileri

Attribute	Value
Yükseklik H2	2,00 mm
Yükseklik H	9,00 mm
Dış çap D1	7,5 mm
Kafa çapı Dk	7,2 mm
İç çap d1	5,8 mm
d2	3,0 mm
İç çap d	3,70 mm
Yay stroku Z	2,0 mm
Çap Ds	5,7 mm
Yükseklik H3	3,20 mm
Çap Dmax(S)	8,0 mm

Not: DIN ISO 3302-1 M3 uyarınca elastomer parçalar için kabul edilebilir boyut toleransları



Tasarım verileri FGA 6 NK-45 N004



WWW.SCHMALZ.COM/10.01.06.02604

Körüklü vantuz (yuvarlak)

FGA 6 NK-45 N004



Art.-Nr.: 10.01.06.02604



Teknik veriler

Attribute	Value
Vantuz malzemesi	Doğal Kauçuk NK
İş parçası yarıçapı dak (dışbükey)	2,0 mm
Emme kuvveti (-600mbar)	0,40 N
Ağırlık	0,20 g
Boyut	6,00
Körük Sayısı	1,5
Ürün ailesi	FGA

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.02604



WWW.SCHMALZ.COM/10.01.06.02604