

Bellows suction cup (round)

FG 19 NK-45 N047




Art.-Nr.: 10.01.06.02612



Technical data

Suction cup material	Natural rubber NK
Material hardness [Shore A]	45.0 Shore A
Size	19.00
Number of folds	2.5

FG 19 NK-45 N047



Design data

Height H2	2.90 mm
Height H	22.30 mm
Outside diameter D1	16.0 mm
Head diameter Dk	16.0 mm
Internal diameter d1	12.0 mm
d2	3.0 mm
Internal diameter d	9.00 mm
Spring stroke Z	6.0 mm
Diameter Ds	19.5 mm
Height H3	4.80 mm
Diameter Dmax(S)	20.7 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Design data FG 19 NK-45 N047



WWW.SCHMALZ.COM/10.01.06.02612

Art.-Nr.: 10.01.06.02612

**Technical data**

Nipple family	N 047
Suction cup material	Natural rubber NK
Material hardness [Shore A]	45.0 Shore A
Hose inner diameter (recom.) d	4.0 mm
Workpiece radius min. (convex)	25.0 mm
Pull-off force	6.40 N
Suction force (-600mbar)	2.60 N
Weight	2.50 g
Volume	1.450 cm ³
Size	19.00
Number of folds	2.5
Product family	FG

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Ordering Data Accessories 10.01.06.02612**

Typ		Item number
Suction cup connection nipple	SA-NIP N047 G1/8-AG DN350	10.01.01.12491

