


Körüklü vantuz (yuvarlak)

FG 19 NK-45 N047

Art.-Nr.: 10.01.06.02612



FG 19 NK-45 N047



Tasarım verileri FG 19 NK-45 N047

Teknik veriler

| | |
|----------------------------|-----------------|
| Vantuz malzemesi | Doğal Kauçuk NK |
| Malzeme sertliği [Shore A] | 45,0 Shore A |
| Boyut | 19,00 |
| Körük Sayısı | 2,5 |

Tasarım verileri

| | |
|--------------|----------|
| Yükseklik H2 | 2,90 mm |
| Yükseklik H | 22,30 mm |
| Dış çap D1 | 16,0 mm |
| Kafa çapı Dk | 16,0 mm |
| İç çap d1 | 12,0 mm |
| d2 | 3,0 mm |
| İç çap d | 9,00 mm |
| Yay stroku Z | 6,0 mm |
| Çap Ds | 19,5 mm |
| Yükseklik H3 | 4,80 mm |
| Çap Dmax(S) | 20,7 mm |

Not: DIN ISO 3302-1 M3 uyarınca elastomer parçalar için kabul edilebilir boyut toleransları



WWW.SCHMALZ.COM/10.01.06.02612

Körüklü vantuz (yuvarlak)

FG 19 NK-45 N047



Art.-Nr.: 10.01.06.02612



Teknik veriler

| | |
|------------------------------------|-----------------------|
| Meme ucu ailesi | N 047 |
| Vantuz malzemesi | Doğal Kauçuk NK |
| Malzeme sertliği [Shore A] | 45,0 Shore A |
| Hortum çapı (tavsiye edilen) d | 4,0 mm |
| İş parçası yarıçapı dak (dışbükey) | 25,0 mm |
| Çekme kuvveti | 6,40 N |
| Emme kuvveti (-600mbar) | 2,60 N |
| Ağırlık | 2,50 g |
| Cilt | 1,450 cm ³ |
| Boyut | 19,00 |
| Körük Sayısı | 2,5 |
| Ürün ailesi | FG |

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Sipariş Verisi Aksesuarlar 10.01.06.02612

| Typ | Ürün numarası |
|--|----------------|
| Vantuz bağlantı nipelı SA-NIP N047 G1/8-AG DN350 | 10.01.01.12491 |



WWW.SCHMALZ.COM/10.01.06.02612