



Art.-Nr.: 10.01.06.02672



FSGPL 150 NBR-55 G1/2-IG DR

Sızdırmazlık halkalı körüklü vantuz, çeşitli çaplarda mevcuttur, sızdırmazlık halkası yapıştırılmış olarak teslim edilir.



Tasarım verileri FSGPL 150 NBR-55 G1/2-IG DR

Teknik veriler

Attribute	Value
Vantuz malzemesi	Nitril kauçuk NBR
Malzeme sertliği [Shore A]	55.0 Shore A
Boyut	150.00
Körük Sayısı	1.5
Meme ucu malzemesi	Çelik

Tasarım verileri

Attribute	Value
Yükseklik H	51.00 mm
Dış çap D1	155.0 mm
d2	93.0 mm
Dış G1	G1/2"-F
Dış uzunluğu LG1	8.0 mm
Delik boyutu d3	69.4 mm
Yay stroku Z	35.7 mm
Çap Ds	115.0 mm
Yükseklik H4	8.00 mm
Çap Dmax(S)	160.0 mm

Art.-Nr.: 10.01.06.02672

**Teknik veriler**

Attribute	Value
Vantuz malzemesi	Nitril kauçuk NBR
Malzeme sertliği [Shore A]	55.0 Shore A
Hortum çapı (tavsiye edilen) d	12.0 mm
İş parçası yarıçapı dak (dışbükey)	250.0 mm
Çekme kuvveti	500.00 N
Emme kuvveti (-600mbar)	370.00 N
Ağırlık	415.0 g
Cilt	443.156 cm ³
Boyut	150.00
Körük Sayısı	1.5
Ürün ailesi	FSGPL

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.02672

WWW.SCHMALZ.COM/10.01.06.02672