


SAB 40 HT1-60 G1/4-IG

Çeşitli çaplarda mevcut olan vantuz SAB HT1, elastomer parçaya vulkanize edilmiş bağlantı nipeli ile birlikte teslim edilir.



Tasarım verileri SAB 40 HT1-60 G1/4-IG

Teknik veriler

Attribute	Value
Vantuz malzemesi	Yüksek sıcaklık malzemesi HT1
Malzeme sertliği [Shore A]	60.0 Shore A
Boyut	40.00
Körük Sayısı	1.5
Bağlantı	G1/4-IG
Meme ucu malzemesi	Alüminyum

Tasarım verileri

Attribute	Value
Yükseklik H	28.80 mm
Dış çap D1	32.0 mm
Nominal çap dn	4.00 mm
Dış G1	G1/4"-F
Dış uzunluğu LG1	12.0 mm
Anahtar boyutu SW1	17.0 mm
Yay stroku Z	9.8 mm
Çap Ds	40.1 mm
Çap Dmax(S)	45.0 mm

Art.-Nr.: 10.01.06.02724

**Teknik veriler**

Attribute	Value
Vantuz malzemesi	Yüksek sıcaklık malzemesi HT1
Malzeme sertliği [Shore A]	60.0 Shore A
Hortum çapı (tavsiye edilen) d	4.0 mm
İş parçası yarıçapı dak (dışbükey)	40.0 mm
Çekme kuvveti	59.00 N
Emme kuvveti (-600mbar)	38.00 N
Ağırlık	14.3 g
Yanal kuvvet	36.0 N
Yanal kuvvet yağlı yüzey	33.0 N
Cilt	8.680 cm ³
Boyut	40.00
Körük Sayısı	1.5
Ürün ailesi	SAB

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.02724

WWW.SCHMALZ.COM/10.01.06.02724