




SAB 60 HT1-60 G3/8-IG

Çeşitli çaplarda mevcut olan vantuz SAB HT1, elastomer parçaya vulkanize edilmiş bağlantı nipeli ile birlikte teslim edilir.

Teknik veriler

Attribute	Value
Vantuz malzemesi	Yüksek sıcaklık malzemesi HT1
Malzeme sertliği [Shore A]	60.0 Shore A
Boyut	60.00
Körük Sayısı	1.5
Bağlantı	G3/8-IG
Meme ucu malzemesi	Alüminyum



Tasarım verileri SAB 60 HT1-60 G3/8-IG

Tasarım verileri

Attribute	Value
Yükseklik H	41.30 mm
Dış çap D1	48.0 mm
Nominal çap dn	6.00 mm
Dış G1	G3/8"-F
Dış uzunluğu LG1	15.0 mm
Anahtar boyutu SW1	22.0 mm
Yay stroku Z	14.5 mm
Çap Ds	61.1 mm
Çap Dmax(S)	67.0 mm

Art.-Nr.: 10.01.06.02726

**Teknik veriler**

Attribute	Value
Vantuz malzemesi	Yüksek sıcaklık malzemesi HT1
Malzeme sertliği [Shore A]	60.0 Shore A
Hortum çapı (tavsiye edilen) d	6.0 mm
İş parçası yarıçapı dak (dışbükey)	65.0 mm
Çekme kuvveti	130.00 N
Emme kuvveti (-600mbar)	82.00 N
Ağırlık	40.0 g
Yanal kuvvet	82.0 N
Yanal kuvvet yağlı yüzey	77.0 N
Cilt	28.800 cm ³
Boyut	60.00
Körük Sayısı	1.5
Ürün ailesi	SAB

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.02726

WWW.SCHMALZ.COM/10.01.06.02726