


Technical data

Attribute	Value
Suction cup material	Natural rubber NK
Material hardness [Shore A]	45.0 Shore A
Size	53.00
Number of folds	1.5
Connection	G1/4"-M
Nipple material	Aluminum

FSGA 53 NK-45 G1/4-AG DR

Bellows suction cup with sealing ring, available in various diameters, delivered with sealing ring glued on.



Design data

Attribute	Value
Height H	40.00 mm
Nominal diameter dn	4.40 mm
d2	33.0 mm
Thread G1	G1/4"-M
Thread length LG1	11.0 mm
Key width SW1	17.0 mm
Spring stroke Z	12.0 mm
Diameter Ds	37.0 mm
Diameter Dmax(S)	60.0 mm

Design data FSGA 53 NK-45 G1/4-AG DR

Art.-Nr.: 10.01.06.02928

**Technical data**

Attribute	Value
Suction cup material	Natural rubber NK
Material hardness [Shore A]	45.0 Shore A
Hose inner diameter (recom.) d	6.0 mm
Workpiece radius min. (convex)	100.0 mm
Pull-off force	95.00 N
Suction force (-600mbar)	51.30 N
Weight	30.2 g
Volume	28.400 cm ³
Size	53.00
Number of folds	1.5
Product family	FSGA

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.02928

**Ordering Data Spare Parts 10.01.06.02928**

Typ	Item number
Suction cup connection nipple	SA-NIP N018 G1/4-AG DN440 10.01.06.01065

**Ordering Data Wear Parts 10.01.06.02928**

Typ	Item number
Bellows suction cup (round)	FGA 53 NK-45 N018 DR 10.01.06.02929

