


Сильфонная присоска (круглая)
FGA 53 NK-45 N018 DR




Art.-Nr.: 10.01.06.02929



FGA 53 NK-45 N018 DR

Технические данные

Attribute	Value
Материал присоски	Натуральная резина НК
Твердость материала [Shore A]	45,0 Shore A
размер	53,00
Количество складок	1,5



Конструктивные данные FGA 53 NK-45 N018 DR

Конструктивные данные

Attribute	Value
Высота H2	12,30 mm
Высота H	36,00 mm
Наружный диаметр D1	58,6 mm
Диаметр головки Dk	18,0 mm
d2	33,0 mm
Внутренний диаметр d	8,00 mm
Ход пружины Z	15,0 mm
Диаметр Ds	39,0 mm
Высота H3	19,00 mm
Диаметр Dmax(S)	60,0 mm



WWW.SCHMALZ.COM/10.01.06.02929

Сильфонная присоска (круглая)
FGA 53 NK-45 N018 DR



Art.-Nr.: 10.01.06.02929



Технические данные

Attribute	Value
Семейство ниппелей	N 018
Материал присоски	Натуральная резина НК
Твердость материала [Shore A]	45,0 Shore A
Радиус заготовки мин. (выпуклый)	75,0 mm
Сила отрыва	95,00 N
Всасывающая сила (-600 мбар)	51,30 N
Вес	18,3 g
Объем	28,400 cm ³
размер	53,00
Количество складок	1,5
Семейство продуктов	FGA

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.02929



WWW.SCHMALZ.COM/10.01.06.02929