




FG 4 NBR-55 N017

Teknik veriler

Attribute	Value
Vantuz malzemesi	Nitril kauçuk NBR
Malzeme sertliği [Shore A]	55,0 Shore A
Boyut	4,00
Körük Sayısı	2,5



Tasarım verileri FG 4 NBR-55 N017

Tasarım verileri

Attribute	Value
Yükseklik H2	3,90 mm
Yükseklik H	14,00 mm
Dış çap D1	5,1 mm
Kafa çapı Dk	7,0 mm
d2	2,4 mm
İç çap d	3,50 mm
Yay stroku Z	1,5 mm
Çap Ds	3,8 mm
Yükseklik H3	7,00 mm
Çap Dmax(S)	5,5 mm

Not: DIN ISO 3302-1 M3 uyarınca elastomer parçalar için kabul edilebilir boyut toleransları

Art.-Nr.: 10.01.06.02962

**Teknik veriler**

Attribute	Value
Meme ucu ailesi	N 017
Vantuz malzemesi	Nitril kauçuk NBR
Malzeme sertliği [Shore A]	55,0 Shore A
İş parçası yarıçapı dak (dışbükey)	4,0 mm
Çekme kuvveti	0,60 N
Emme kuvveti (-600mbar)	0,27 N
Ağırlık	0,40 g
Cilt	0,124 cm ³
Boyut	4,00
Körük Sayısı	2,5
Ürün ailesi	FG

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.02962

WWW.SCHMALZ.COM/10.01.06.02962