


Art.-Nr.: 10.01.06.02985




Teknik veriler

Attribute	Value
Vantuz malzemesi	Nitril kauçuk NBR
Malzeme sertliği [Shore A]	55.0 Shore A
Boyut	200.00
Körük Sayısı	1.5
Meme ucu malzemesi	Çelik

FSGPL 200 NBR-55 G1/2-IG DR

Sızdırmazlık halkalı körüklü vantuz, çeşitli çaplarda mevcuttur, sızdırmazlık halkası yapıştırılmış olarak teslim edilir.



Tasarım verileri

Attribute	Value
Yükseklik H	54.00 mm
Dış çap D1	202.0 mm
d2	137.0 mm
Dış G1	G1/2"-F
Dış uzunluğu LG1	8.0 mm
Delik boyutu d3	119.4 mm
Yay stroku Z	37.2 mm
Çap Ds	164.0 mm
Yükseklik H4	8.00 mm
Çap Dmax(S)	208.0 mm

Tasarım verileri FSGPL 200 NBR-55 G1/2-IG DR

Art.-Nr.: 10.01.06.02985



Teknik veriler

Attribute	Value
Vantuz malzemesi	Nitril kauçuk NBR
Malzeme sertliği [Shore A]	55.0 Shore A
Hortum çapı (tavsiye edilen) d	12.0 mm
Ağırlık	1038.9 g
Boyut	200.00
Körük Sayısı	1.5
Ürün ailesi	FSGPL

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.02985

