



Art.-Nr.: 10.01.06.02993



FSGPL 120 NBR-55 G1/2-IG DR

Sızdırmazlık halkalı körüklü vantuz, çeşitli çaplarda mevcuttur, sızdırmazlık halkası yapıştırılmış olarak teslim edilir.



Tasarım verileri FSGPL 120 NBR-55 G1/2-IG DR

Teknik veriler

Attribute	Value
Vantuz malzemesi	Nitril kauçuk NBR
Malzeme sertliği [Shore A]	55.0 Shore A
Boyut	120.00
Körük Sayısı	1.5
Meme ucu malzemesi	Çelik

Tasarım verileri

Attribute	Value
Yükseklik H	51.00 mm
Dış çap D1	127.8 mm
d2	79.3 mm
Dış G1	G1/2"-F
Dış uzunluğu LG1	8.0 mm
Delik boyutu d3	69.4 mm
Yay stroku Z	35.7 mm
Çap Ds	96.0 mm
Yükseklik H4	8.00 mm
Çap Dmax(S)	135.0 mm

Art.-Nr.: 10.01.06.02993



Teknik veriler

Attribute	Value
Vantuz malzemesi	Nitril kauçuk NBR
Malzeme sertliği [Shore A]	55.0 Shore A
Hortum çapı (tavsiye edilen) d	12.0 mm
İş parçası yarıçapı dak (dışbükey)	150.0 mm
Ağırlık	354.0 g
Cilt	290.675 cm ³
Boyut	120.00
Körük Sayısı	1.5
Ürün ailesi	FSGPL

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.02993



WWW.SCHMALZ.COM/10.01.06.02993