


Art.-Nr.: 10.01.06.03143



FGA 14 SI-HD-65 N016

Teknik veriler

Attribute	Value
Vantuz malzemesi	Silikon SI-HD
Malzeme sertliği [Shore A]	65.0 Shore A
Boyut	14.00
Körük Sayısı	1.5
Malzeme özellikleri	FDA uyumlu



Tasarım verileri FGA 14 SI-HD-65 N016

Tasarım verileri

Attribute	Value
Yükseklik H2	3.80 mm
Yükseklik H	15.50 mm
Dış çap D1	13.7 mm
Kafa çapı Dk	10.0 mm
d2	5.0 mm
İç çap d	4.50 mm
Yay stroku Z	5.0 mm
Çap Ds	12.5 mm
Yükseklik H3	8.50 mm
Çap Dmax(S)	14.5 mm

Not: DIN ISO 3302-1 M3 uyarınca elastomer parçalar için kabul edilebilir boyut toleransları

Art.-Nr.: 10.01.06.03143

**Teknik veriler**

Attribute	Value
Vantuz malzemesi	Silikon SI-HD
İş parçası yarıçapı dak (dışbükey)	12.5 mm
Emme kuvveti (-600mbar)	1.20 N
Ağırlık	1.0 g
Boyut	14.00
Körük Sayısı	1.5
Ürün ailesi	FGA

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.03143

**Veri aksesuarları sipariş edin 10.01.06.03143**

Typ		Ürün numarası
Vantuz bağlantı nipeli	SA-NIP N016 G1/8-AG DN350	10.01.06.05735
Vantuz bağlantı nipeli	SA-NIP N016 G1/8-IG DN350	10.01.06.05731
Vantuz bağlantı nipeli	SA-NIP N016 M5-AG DN250	10.01.06.00123
Vantuz bağlantı nipeli	SA-NIP N016 G1/8-AG DN310	10.01.06.04062
Vantuz bağlantı nipeli	SA-NIP N016 M5-AG DN250	10.01.06.04365
Vantuz bağlantı nipeli	SA-NIP N016 M5-IG DN310	10.01.06.04689
Vantuz bağlantı nipeli	SA-NIP N016 G1/8-IG DN310	10.01.06.04690

WWW.SCHMALZ.COM/10.01.06.03143