

Bellows suction cup SI-HD (round)  
**FG 25 SI-HD-65 N016**




Art.-Nr.: 10.01.06.03246



**Technical data**

Suction cup material	Silicone SI-HD
Material hardness [Shore A]	65.0 Shore A
Size	25.00
Number of folds	2.5
Material characteristics	FDA-compatible

FG 25 SI-HD-65 N016



**Design data**

Height H2	3.80 mm
Height H	34.00 mm
Outside diameter D1	25.0 mm
Head diameter Dk	10.0 mm
d2	10.0 mm
Internal diameter d	4.50 mm
Spring stroke Z	18.0 mm
Diameter Ds	23.0 mm
Height H3	9.00 mm
Diameter Dmax(S)	26.0 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Design data FG 25 SI-HD-65 N016



[WWW.SCHMALZ.COM/10.01.06.03246](http://WWW.SCHMALZ.COM/10.01.06.03246)

Bellows suction cup SI-HD (round)  
**FG 25 SI-HD-65 N016**



Art.-Nr.: 10.01.06.03246



**Technical data**

Nipple family	N 016
Suction cup material	Silicone SI-HD
Material hardness [Shore A]	65.0 Shore A
Hose inner diameter (recom.) d	4.0 mm
Workpiece radius min. (convex)	30.0 mm
Pull-off force	19.00 N
Suction force (-600mbar)	4.50 N
Weight	4.10 g
Volume	5.222 cm <sup>3</sup>
Size	25.00
Number of folds	2.5
Product family	FG

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



**Ordering Data Accessories 10.01.06.03246**

Typ		Item number
Suction cup connection nipple	SA-NIP N016 G1/8-AG DN350	10.01.06.05735
Suction cup connection nipple	SA-NIP N016 G1/8-IG DN350	10.01.06.05731
Suction cup connection nipple	SA-NIP N016 M5-AG DN250	10.01.06.00123
Suction cup connection nipple	SA-NIP N016 G1/8-AG DN310	10.01.06.04062
Suction cup connection nipple	SA-NIP N016 M5-AG DN250	10.01.06.04365
Suction cup connection nipple	SA-NIP N016 M5-IG DN310	10.01.06.04689
Suction cup connection nipple	SA-NIP N016 G1/8-IG DN310	10.01.06.04690



[WWW.SCHMALZ.COM/10.01.06.03246](http://WWW.SCHMALZ.COM/10.01.06.03246)