

Körüklü vantuz 2C (yuvarlak)

SDC2 20 PU 30/60 N042


Art.-Nr.: 10.01.06.03365



SDC2 20 PU 30/60 N042

Teknik veriler

Attribute	Value
Vantuz malzemesi	Poliüretan PU
Malzeme sertliği [Shore A]	30.0 Shore A
Boyut	20.00
Körük Sayısı	2.5
Malzeme sertliği	60.0 Shore A



Tasarım verileri SDC2 20 PU 30/60 N042

Tasarım verileri

Attribute	Value
Yükseklik H2	4.50 mm
Yükseklik H	14.50 mm
Dış çap D1	20.0 mm
Kafa çapı Dk	12.0 mm
İç çap d1	7.2 mm
d2	11.5 mm
İç çap d	5.00 mm
Yay stroku Z	7.5 mm
Çap Ds	21.0 mm
Yükseklik H3	6.50 mm



WWW.SCHMALZ.COM/10.01.06.03365

Art.-Nr.: 10.01.06.03365



Teknik veriler

Attribute	Value
Vantuz malzemesi	Poliüretan PU
Malzeme sertliği [Shore A]	30.0 Shore A
İş parçası yarıçapı dak (dışbükey)	10.0 mm
Çekme kuvveti	15.00 N
Emme kuvveti (-600mbar)	6.20 N
Boyut	20.00
Sıcaklık direnci	55.0 °C
Körük Sayısı	2.5
Malzeme sertliği	60.0 Shore A

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.03365

