

Körüklü vantuz 2C (yuvarlak)

SDC2 40 PU 30/60 N043


Art.-Nr.: 10.01.06.03367



SDC2 40 PU 30/60 N043

Teknik veriler

Attribute	Value
Vantuz malzemesi	Poliüretan PU
Malzeme sertliği [Shore A]	30.0 Shore A
Boyut	40.00
Körük Sayısı	2.5
Malzeme sertliği	60.0 Shore A



Tasarım verileri SDC2 40 PU 30/60 N043

Tasarım verileri

Attribute	Value
Yükseklik H2	6.00 mm
Yükseklik H	28.40 mm
Dış çap D1	34.0 mm
Kafa çapı Dk	22.0 mm
İç çap d1	10.0 mm
d2	17.0 mm
İç çap d	6.50 mm
Yay stroku Z	14.0 mm
Çap Ds	40.0 mm
Yükseklik H3	11.50 mm



WWW.SCHMALZ.COM/10.01.06.03367

Körüklü vantuz 2C (yuvarlak)

SDC2 40 PU 30/60 N043



Art.-Nr.: 10.01.06.03367



Teknik veriler

Attribute	Value
Vantuz malzemesi	Poliüretan PU
Malzeme sertliği [Shore A]	30.0 Shore A
İş parçası yarıçapı dak (dışbükey)	15.0 mm
Çekme kuvveti	50.00 N
Emme kuvveti (-600mbar)	13.60 N
Boyut	40.00
Sıcaklık direnci	55.0 °C
Körük Sayısı	2.5
Malzeme sertliği	60.0 Shore A

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.03367



WWW.SCHMALZ.COM/10.01.06.03367