

Сильфонная присоска 2К (круглая)
SDC2 40 PU 30/60 N043




Art.-Nr.: 10.01.06.03367



SDC2 40 PU 30/60 N043

Технические данные

Attribute	Value
Материал присоски	Полиуретан PU
Твердость материала [Shore A]	30,0 Shore A
размер	40,00
Количество складок	2,5
Твердость материала	60,0 Shore A



Конструктивные данные SDC2 40 PU 30/60 N043

Конструктивные данные

Attribute	Value
Высота H2	6,00 mm
Высота H	28,40 mm
Наружный диаметр D1	34,0 mm
Диаметр головки Dk	22,0 mm
Внутренний диаметр d1	10,0 mm
d2	17,0 mm
Внутренний диаметр d	6,50 mm
Ход пружины Z	14,0 mm
Диаметр Ds	40,0 mm
Высота H3	11,50 mm



WWW.SCHMALZ.COM/10.01.06.03367

Сильфонная присоска 2К (круглая)
SDC2 40 PU 30/60 N043



Art.-Nr.: 10.01.06.03367



Технические данные

Attribute	Value
Материал присоски	Полиуретан PU
Твердость материала [Shore A]	30,0 Shore A
Радиус заготовки мин. (выпуклый)	15,0 mm
Сила отрыва	50,00 N
Всасывающая сила (-600 мбар)	13,60 N
размер	40,00
Термостойкость	55,0 °C
Количество складок	2,5
Твердость материала	60,0 Shore A

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.03367



WWW.SCHMALZ.COM/10.01.06.03367