

Bellows suction cups (round)

SPB4f 40 SI-55 G1/8-IG



Art.-Nr.: 10.01.06.03547



Technical data

Attribute	Value
Suction cup material	Silicone SI
Material hardness [Shore A]	55.0 Shore A
Size	40.00
Number of folds	4.5
Thread G1	G1/8"-F


SPB4f 40 SI-55 G1/8-IG

Suction cup SPB4f (elastomer part + connection element) with integrated bag stabilizer is delivered assembled. The assembly consists of:

- Suction cup of type SPB4f – elastomer part, available in various diameters
- Connection element of type SC – available with various threads

Available spare parts: suction cup SPB4f, Schmalz-Connector

Available accessories: filter screen (sieve, round), hose clamp



Design data

Attribute	Value
Height H	69.50 mm
Nominal diameter dn	8.60 mm
d2	15.3 mm
Thread G1	G1/8"-F
Thread length LG1	12.0 mm
Key width SW1	22.0 mm
Spring stroke Z	18.0 mm
Diameter Ds	39.7 mm
Diameter Dmax(S)	42.0 mm

Design data SPB4f 40 SI-55 G1/8-IG



WWW.SCHMALZ.COM/10.01.06.03547

Bellows suction cups (round)

SPB4f 40 SI-55 G1/8-IG



Art.-Nr.: 10.01.06.03547



Technical data

Attribute	Value
Suction cup material	Silicone SI
Material hardness [Shore A]	55.0 Shore A
Hose inner diameter (recom.) d	9.0 mm
Pull-off force	23.80 N
Suction force (-600mbar)	20.40 N
Weight	35.5 g
Volume	15.120 cm ³
Number of folds	4.5
Suction force at -400 mbar	13.60 N
Suction force at -200 mbar	6.80 N
Product family	SPB4f

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.03547



Ordering Data Accessories 10.01.06.03547

Typ		Item number
Hose clamp	SSB 16-27 ST-VZ	10.07.10.00002



Ordering Data Spare Parts 10.01.06.03547

Typ		Item number
Schmalz-Connector	SC 080 G1/8-IG	10.01.06.03270
Bellows suction cup (round)	SPB4f 40 SI-55 SC080	10.01.06.03265



WWW.SCHMALZ.COM/10.01.06.03547