


Art.-Nr.: 10.01.06.03625



Teknik veriler

Attribute	Value
Vantuz malzemesi	Silikon SI
Malzeme sertliği [Shore A]	55.0 Shore A
Boyutlar (LxW)	35 x 15
Körük Sayısı	1.5

SPOB1f 35x15 SI-55 SC040-AR



Tasarım verileri

Attribute	Value
Uzunluk L1	35.00 mm
Genişlik B1	15.00 mm
Yükseklik H2	5.00 mm
Yükseklik H	13.00 mm
Kafa uzunluğu Lk	28.50 mm
İç çap d1	11.0 mm
İç çap d	8.30 mm
Yay stroku Z	4.0 mm
Vantuz genişliği Bs	14.60 mm
Ls	34.60 mm

Tasarım verileri SPOB1f 35x15 SI-55 SC040-AR



Art.-Nr.: 10.01.06.03625

**Teknik veriler**

Attribute	Value
Meme ucu ailesi	SC 040-AR
Vantuz malzemesi	Silikon SI
Malzeme sertliği [Shore A]	55.0 Shore A
Hortum çapı (tavsiye edilen) d	6.0 mm
Emme kuvveti (-600mbar)	12.60 N
Ağırlık	1.7 g
Boyutlar (LxW)	35 x 15
Cilt	2.139 cm ³
Körük Sayısı	1.5
400 mbar'da emme kuvveti	8.40 N
200 mbar'da emme kuvveti	4.20 N
Ürün ailesi	SPOB1f
Dak iş parçası genişliği	10.0 mm

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.03625

**Veri aksesuarları sipariş edin 10.01.06.03625**

Typ	Ürün numarası
Schmalz-Konnektör	SC 040-AR NPT1/8-AG MOD
	10.01.06.02581

