


Art.-Nr.: 10.01.06.03625



Технические данные

Attribute	Value
Материал присоски	Силикон SI
Твердость материала [Shore A]	55,0 Shore A
Размеры (ДxШ)	35 x 15
Количество складок	1,5

SPOB1f 35x15 SI-55 SC040-AR



Конструктивные данные

Attribute	Value
Длина L1	35,00 mm
Ширина B1	15,00 mm
Высота H2	5,00 mm
Высота H	13,00 mm
Длина головы Lk	28,50 mm
Внутренний диаметр d1	11,0 mm
Внутренний диаметр d	8,30 mm
Ход пружины Z	4,0 mm
Ширина присоски Bs	14,60 mm
Ls	34,60 mm

Конструктивные данные SPOB1f 35x15 SI-55 SC040-AR



Art.-Nr.: 10.01.06.03625



Технические данные

Attribute	Value
Семейство ниппелей	SC 040-AR
Материал присоски	Силикон SI
Твердость материала [Shore A]	55,0 Shore A
Внутренний диаметр шланга (реком.) d	6,0 mm
Всасывающая сила (-600 мбар)	12,60 N
Вес	1,7 g
Размеры (ДхШ)	35 x 15
Объем	2,139 cm ³
Количество складок	1,5
Всасывающая сила при -400 мбар	8,40 N
Всасывающая сила при -200 мбар	4,20 N
Семейство продуктов	SPOB1f
Мин. ширина заготовки	10,0 mm

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.03625

Данные для заказа Аксессуары **10.01.06.03625**

Тип	Количество предметов
Соединитель Schmalz SC 040-AR NPT1/8-AG MOD	10.01.06.02581

