


Art.-Nr.: 10.01.06.03626



SPOB1f 60x25 SI-55 SC050-AR

Teknik veriler

Attribute	Value
Vantuz malzemesi	Silikon SI
Malzeme sertliği [Shore A]	55.0 Shore A
Boyutlar (LxW)	60 x 25
Körük Sayısı	1.5



Tasarım verileri SPOB1f 60x25 SI-55 SC050-AR

Tasarım verileri

Attribute	Value
Uzunluk L1	60.00 mm
Genişlik B1	25.00 mm
Yükseklik H2	6.90 mm
Yükseklik H	23.00 mm
Kafa uzunluğu Lk	46.90 mm
İç çap d1	17.3 mm
İç çap d	12.40 mm
Yay stroku Z	9.0 mm
Vantuz genişliği Bs	24.50 mm
Ls	59.50 mm

Art.-Nr.: 10.01.06.03626

**Teknik veriler**

Attribute	Value
Meme ucu ailesi	SC 050-AR
Vantuz malzemesi	Silikon SI
Malzeme sertliği [Shore A]	55.0 Shore A
Hortum çapı (tavsiye edilen) d	8.0 mm
Emme kuvveti (-600mbar)	36.60 N
Ağırlık	6.7 g
Boyutlar (LxW)	60 x 25
Cilt	11.535 cm ³
Körük Sayısı	1.5
400 mbar'da emme kuvveti	24.40 N
200 mbar'da emme kuvveti	12.20 N
Ürün ailesi	SPOB1f
Dak iş parçası genişliği	20.0 mm

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.03626

**Veri aksesuarları sipariş edin 10.01.06.03626**

Typ	Ürün numarası
Schmalz-Konnektör	SC 050-AR NPT1/4-AG MOD
Schmalz-Konnektör	SC 050-AR NPT1/4-IG MOD

