




Teknik veriler

Attribute	Value
Vantuz malzemesi	Silikon SI
Malzeme sertliği [Shore A]	55.0 Shore A
Boyutlar (LxW)	80 x 35
Körük Sayısı	1.5

SPOB1f 80x35 SI-55 SC050-AR



Tasarım verileri

Attribute	Value
Uzunluk L1	80.00 mm
Genişlik B1	35.00 mm
Yükseklik H2	6.90 mm
Yükseklik H	27.00 mm
Kafa uzunluğu Lk	61.10 mm
İç çap d1	17.3 mm
İç çap d	12.40 mm
Yay stroku Z	11.0 mm
Vantuz genişliği Bs	34.50 mm
Ls	79.50 mm

Tasarım verileri SPOB1f 80x35 SI-55 SC050-AR

Art.-Nr.: 10.01.06.03627

**Teknik veriler**

Attribute	Value
Meme ucu ailesi	SC 050-AR
Vantuz malzemesi	Silikon SI
Malzeme sertliği [Shore A]	55.0 Shore A
Hortum çapı (tavsiye edilen) d	8.0 mm
Emme kuvveti (-600mbar)	74.70 N
Ağırlık	12.6 g
Boyutlar (LxW)	80 x 35
Cilt	26.122 cm ³
Körük Sayısı	1.5
400 mbar'da emme kuvveti	49.80 N
200 mbar'da emme kuvveti	24.90 N
Ürün ailesi	SPOB1f
Dak iş parçası genişliği	30.0 mm

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.03627

**Veri aksesuarları sipariş edin 10.01.06.03627**

Typ	Ürün numarası
Schmalz-Konnektör	SC 050-AR NPT1/4-AG MOD
Schmalz-Konnektör	SC 050-AR NPT1/4-IG MOD

