




SAB 80 HT1-60 G1/2-IG

Çeşitli çaplarda mevcut olan vantuz SAB HT1, elastomer parçaya vulkanize edilmiş bağlantı nipeli ile birlikte teslim edilir.

Teknik veriler

Attribute	Value
Vantuz malzemesi	Yüksek sıcaklık malzemesi HT1
Malzeme sertliği [Shore A]	60.0 Shore A
Boyut	80.00
Körük Sayısı	1.5
Bağlantı	G1/2-IG
Meme ucu malzemesi	Alüminyum



Tasarım verileri SAB 80 HT1-60 G1/2-IG

Tasarım verileri

Attribute	Value
Yükseklik H	49.90 mm
Dış çap D1	63.6 mm
Nominal çap dn	6.00 mm
Dış G1	G1/2"-F
Dış uzunluğu LG1	15.0 mm
Anahtar boyutu SW1	24.0 mm
Yay stroku Z	22.1 mm
Çap Ds	81.1 mm
Çap Dmax(S)	89.0 mm

Art.-Nr.: 10.01.06.03632

**Teknik veriler**

Attribute	Value
Vantuz malzemesi	Yüksek sıcaklık malzemesi HT1
Malzeme sertliği [Shore A]	60.0 Shore A
Hortum çapı (tavsiye edilen) d	6.0 mm
İş parçası yarıçapı dak (dışbükey)	75.0 mm
Çekme kuvveti	221.00 N
Emme kuvveti (-600mbar)	135.00 N
Ağırlık	57.8 g
Yanal kuvvet	145.0 N
Yanal kuvvet yağlı yüzey	140.0 N
Cilt	67.600 cm ³
Boyut	80.00
Körük Sayısı	1.5
Ürün ailesi	SAB

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.03632

WWW.SCHMALZ.COM/10.01.06.03632