

Bellows suction cups (round)  
**SPB2f 30 SI-55 G1/8-IG**



Art.-Nr.: 10.01.06.03699



**Technical data**


Suction cup material	Silicone SI
Material hardness [Shore A]	55.0 Shore A
Size	30.00
Number of folds	2.5
Thread G1	G1/8"-F

SPB2f 30 SI-55 G1/8-IG

Suction cup SPB2f (elastomer part + connection element) is delivered assembled. The assembly consists of:

- Suction cup of type SPB2f - elastomer part, available in various diameters
- Connection element of type SC - available with various threads

Available spare parts: suction cup SPB2f, Schmalz-Connector



**Design data**

Height H	49.80 mm
Nominal diameter dn	8.60 mm
d2	7.2 mm
Thread G1	G1/8"-F
Thread length LG1	12.0 mm
Key width SW1	22.0 mm
Spring stroke Z	5.0 mm
Diameter Ds	30.0 mm
Diameter Dmax(S)	32.0 mm

Design data SPB2f 30 SI-55 G1/8-IG



[WWW.SCHMALZ.COM/10.01.06.03699](http://WWW.SCHMALZ.COM/10.01.06.03699)

Bellows suction cups (round)  
**SPB2f 30 SI-55 G1/8-IG**



Art.-Nr.: 10.01.06.03699



**Technical data**

Suction cup material	Silicone SI
Material hardness [Shore A]	55.0 Shore A
Hose inner diameter (recom.) d	9.0 mm
Suction force (-600mbar)	12.80 N
Weight	29.70 g
Volume	7.183 cm <sup>3</sup>
Size	30.00
Number of folds	2.5
Suction force at -400 mbar	8.50 N
Suction force at -200 mbar	4.30 N
Product family	SPB2f

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



**Ordering Data Accessories 10.01.06.03699**

Typ		Item number
Hose clamp	SSB 16-27 ST-VZ	10.07.10.00002



**Ordering Data Spare Parts 10.01.06.03699**

Typ		Item number
Schmalz-Connector	SC 080 G1/8-IG	10.01.06.03270



**Ordering Data Wear Parts 10.01.06.03699**

Typ		Item number
Bellows suction cup (round)	SPB2f 30 SI-55 SC080	10.01.06.03643



[WWW.SCHMALZ.COM/10.01.06.03699](http://WWW.SCHMALZ.COM/10.01.06.03699)