



FG 3 NBR-55 N055


Teknik veriler

Attribute	Value
Vantuz malzemesi	Nitril kauçuk NBR
Malzeme sertliği [Shore A]	55.0 Shore A
Boyut	3.00
Körük Sayısı	2.5

Tasarım verileri

Attribute	Value
Yükseklik H2	2.10 mm
Yükseklik H	6.70 mm
Dış çap D1	3.6 mm
Kafa çapı Dk	3.6 mm
İç çap d1	2.3 mm
d2	1.8 mm
İç çap d	1.70 mm
Yay stroku Z	1.1 mm
Çap Ds	3.0 mm
Yükseklik H3	2.70 mm

Not: DIN ISO 3302-1 M3 uyarınca elastomer parçalar için kabul edilebilir boyut toleransları



Tasarım verileri FG 3 NBR-55 N055

Art.-Nr.: 10.01.06.03704

**Teknik veriler**

Attribute	Value
Meme ucu ailesi	N 055
Vantuz malzemesi	Nitril kauçuk NBR
Malzeme sertliği [Shore A]	55.0 Shore A
Hortum çapı (tavsiye edilen) d	2.0 mm
İş parçası yarıçapı dak (dışbükey)	4.0 mm
Çekme kuvveti	0.40 N
Emme kuvveti (-600mbar)	0.15 N
Cilt	0.022 cm ³
Boyut	3.00
Körük Sayısı	2.5
Ürün ailesi	FG

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.03704

WWW.SCHMALZ.COM/10.01.06.03704