

Körüklü vantuz (yuvarlak)
FG 3 SI-55 N055




Art.-Nr.: 10.01.06.03705



FG 3 SI-55 N055

Teknik veriler

Attribute	Value
Vantuz malzemesi	Silikon SI
Malzeme sertliği [Shore A]	55,0 Shore A
Boyut	3,00
Körük Sayısı	2,5
Malzeme özellikleri	FDA uyumlu



Tasarım verileri FG 3 SI-55 N055

Tasarım verileri

Attribute	Value
Yükseklik H2	2,10 mm
Yükseklik H	6,70 mm
Dış çap D1	3,6 mm
Kafa çapı Dk	3,6 mm
İç çap d1	2,3 mm
d2	1,8 mm
İç çap d	1,70 mm
Yay stroku Z	1,1 mm
Çap Ds	3,0 mm
Yükseklik H3	2,70 mm
Çap Dmax(S)	4,0 mm

Not: DIN ISO 3302-1 M3 uyarınca elastomer parçalar için kabul edilebilir boyut toleransları



WWW.SCHMALZ.COM/10.01.06.03705

Körüklü vantuz (yuvarlak)
FG 3 SI-55 N055



Art.-Nr.: 10.01.06.03705



Teknik veriler

Attribute	Value
Meme ucu ailesi	N 055
Vantuz malzemesi	Silikon SI
Malzeme sertliği [Shore A]	55,0 Shore A
Hortum çapı (tavsiye edilen) d	2,0 mm
İş parçası yarıçapı dak (dışbükey)	4,0 mm
Çekme kuvveti	0,40 N
Emme kuvveti (-600mbar)	0,15 N
Cilt	0,022 cm ³
Boyut	3,00
Körük Sayısı	2,5
Ürün ailesi	FG

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.03705



WWW.SCHMALZ.COM/10.01.06.03705