

Körüklü vantuz 2C (yuvarlak)

SDC1 30 PU 30/60 N043


Art.-Nr.: 10.01.06.04049



SDC1 30 PU 30/60 N043

Teknik veriler

Attribute	Value
Vantuz malzemesi	Poliüretan PU
Malzeme sertliği [Shore A]	30.0 Shore A
Boyut	30.00
Körük Sayısı	1.5
Malzeme sertliği	60.0 Shore A



Tasarım verileri SDC1 30 PU 30/60 N043

Tasarım verileri

Attribute	Value
Yükseklik H2	6.00 mm
Yükseklik H	16.80 mm
Dış çap D1	31.8 mm
Kafa çapı Dk	16.8 mm
İç çap d1	10.0 mm
d2	18.0 mm
İç çap d	6.50 mm
Yay stroku Z	7.5 mm
Çap Ds	30.0 mm
Yükseklik H3	9.30 mm



WWW.SCHMALZ.COM/10.01.06.04049

Art.-Nr.: 10.01.06.04049



Teknik veriler

Attribute	Value
Vantuz malzemesi	Poliüretan PU
Malzeme sertliği [Shore A]	30.0 Shore A
İş parçası yarıçapı dak (dışbükey)	15.0 mm
Çekme kuvveti	32.60 N
Emme kuvveti (-600mbar)	15.30 N
Cilt	4.200 cm ³
Boyut	30.00
Sıcaklık direnci	55.0 °C
Körük Sayısı	1.5
Malzeme sertliği	60.0 Shore A

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.04049



WWW.SCHMALZ.COM/10.01.06.04049