


Körüklü vantuz (yuvarlak)


SPB2f 15 SI-55 SC040



Art.-Nr.: 10.01.06.04090



SPB2f 15 SI-55 SC040



Tasarım verileri SPB2f 15 SI-55 SC040

Teknik veriler

Attribute	Value
Vantuz malzemesi	Silikon SI
Malzeme sertliği [Shore A]	55,0 Shore A
Boyut	15,00
Körük Sayısı	2,5
Malzeme özellikleri	FDA uyumlu

Tasarım verileri

Attribute	Value
Yükseklik H2	4,60 mm
Yükseklik H	20,30 mm
Dış çap D1	14,0 mm
Kafa çapı Dk	13,1 mm
İç çap d1	10,5 mm
d2	4,0 mm
İç çap d	7,50 mm
Yay stroku Z	7,3 mm
Çap Ds	15,0 mm
Yükseklik H3	6,60 mm
Çap Dmax(S)	17,0 mm



WWW.SCHMALZ.COM/10.01.06.04090

Art.-Nr.: 10.01.06.04090



Teknik veriler

Attribute	Value
Meme ucu ailesi	SC 040
Vantuz malzemesi	Silikon SI
Malzeme sertliği [Shore A]	55,0 Shore A
Emme kuvveti (-600mbar)	0,75 N
Ağırlık	1,50 g
Cilt	1,200 cm ³
Boyut	15,00
Körük Sayısı	2,5
400 mbar'da emme kuvveti	0,50 N
200 mbar'da emme kuvveti	0,25 N
Ürün ailesi	SPB2f

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.04090



WWW.SCHMALZ.COM/10.01.06.04090