



FGA 4 NBR-ESD-55 N003


Teknik veriler

Attribute	Value
Vantuz malzemesi	Nitril kauçuk NBR-ESD
Malzeme sertliği [Shore A]	55,0 Shore A
Boyut	4,00
Körük Sayısı	1,5

Tasarım verileri

Attribute	Value
Yükseklik H2	1,50 mm
Yükseklik H	5,50 mm
Dış çap D1	4,6 mm
Kafa çapı Dk	4,0 mm
İç çap d1	3,0 mm
d2	2,5 mm
İç çap d	2,00 mm
Yay stroku Z	1,5 mm
Çap Ds	4,0 mm
Yükseklik H3	2,60 mm

Not: DIN ISO 3302-1 M3 uyarınca elastomer parçalar için kabul edilebilir boyut toleransları



Tasarım verileri FGA 4 NBR-ESD-55 N003

Art.-Nr.: 10.01.06.04095

**Teknik veriler**

Attribute	Value
Vantuz malzemesi	Nitril kauçuk NBR-ESD
İş parçası yarıçapı dak (dışbükey)	1,5 mm
Emme kuvveti (-600mbar)	0,29 N
Ağırlık	0,10 g
Boyut	4,00
Körük Sayısı	1,5
Ürün ailesi	FGA

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.04095

**Sipariş Verisi Aksesuarlar 10.01.06.04095**

Typ	Ürün numarası
Vantuz bağlantı nipel	SA-NIP N003 M3-AG DN100
	10.01.01.00316

WWW.SCHMALZ.COM/10.01.06.04095