



FGA 11 NBR-ESD-55 N062


Teknik veriler

Attribute	Value
Vantuz malzemesi	Nitril kauçuk NBR-ESD
Malzeme sertliği [Shore A]	55,0 Shore A
Boyut	11,00
Körük Sayısı	1,5

Tasarım verileri

Attribute	Value
Yükseklik H2	3,80 mm
Yükseklik H	16,00 mm
Dış çap D1	12,0 mm
Kafa çapı Dk	10,0 mm
d2	5,0 mm
İç çap d	4,50 mm
Yay stroku Z	4,0 mm
Çap Ds	10,4 mm
Yükseklik H3	9,30 mm
Çap Dmax(S)	13,0 mm

Not: DIN ISO 3302-1 M3 uyarınca elastomer parçalar için kabul edilebilir boyut toleransları



Tasarım verileri FGA 11 NBR-ESD-55 N062

Art.-Nr.: 10.01.06.04136

**Teknik veriler**

Attribute	Value
Vantuz malzemesi	Nitril kauçuk NBR-ESD
İş parçası yarıçapı dak (dışbükey)	5,0 mm
Emme kuvveti (-600mbar)	1,20 N
Ağırlık	0,90 g
Boyut	11,00
Körük Sayısı	1,5
Ürün ailesi	FGA

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.04136

**Sipariş Verisi Aksesuarlar 10.01.06.04136**

Typ	Ürün numarası
Vantuz bağlantı nipeli	SA-NIP N062 M5-AG DN250
Vantuz bağlantı nipeli	SA-NIP N062 G1/8-IG DN350
Vantuz bağlantı nipeli	SA-NIP N062 G1/8-AG DN350

WWW.SCHMALZ.COM/10.01.06.04136