

FG 7 NBR-ESD-55 N062


Teknik veriler

Attribute	Value
Vantuz malzemesi	Nitril kauçuk NBR-ESD
Malzeme sertliği [Shore A]	55,0 Shore A
Boyut	7,00
Körük Sayısı	2,5

Tasarım verileri

Attribute	Value
Yükseklik H2	3,80 mm
Yükseklik H	14,00 mm
Dış çap D1	6,5 mm
Kafa çapı Dk	9,0 mm
d2	1,8 mm
İç çap d	4,50 mm
Yay stroku Z	3,0 mm
Çap Ds	5,9 mm
Yükseklik H3	6,50 mm
Çap Dmax(S)	7,0 mm

Not: DIN ISO 3302-1 M3 uyarınca elastomer parçalar için kabul edilebilir boyut toleransları



Tasarım verileri FG 7 NBR-ESD-55 N062

Art.-Nr.: 10.01.06.04139

**Teknik veriler**

Attribute	Value
Vantuz malzemesi	Nitril kauçuk NBR-ESD
Malzeme sertliği [Shore A]	55,0 Shore A
İş parçası yarıçapı dak (dışbükey)	7,5 mm
Çekme kuvveti	0,90 N
Emme kuvveti (-600mbar)	0,15 N
Ağırlık	0,50 g
Cilt	0,162 cm ³
Boyut	7,00
Körük Sayısı	2,5
Ürün ailesi	FG

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.04139

**Sipariş Verisi Aksesuarlar 10.01.06.04139**

Typ	Ürün numarası
Vantuz bağlantı nipel	SA-NIP N062 M5-AG DN250
Vantuz bağlantı nipel	SA-NIP N062 G1/8-IG DN350
Vantuz bağlantı nipel	SA-NIP N062 G1/8-AG DN350

