


Körüklü vantuz SI-HD (yuvarlak)  
**FG 20 SI-HD-65 N016**



Art.-Nr.: 10.01.06.04149



FG 20 SI-HD-65 N016



Tasarım verileri FG 20 SI-HD-65 N016

### Teknik veriler

Vantuz malzemesi	Silikon SI-HD
Malzeme sertliği [Shore A]	65,0 Shore A
Boyut	20,00

### Tasarım verileri

Yükseklik H2	3,80 mm
Yükseklik H	22,10 mm
Dış çap D1	20,0 mm
Kafa çapı Dk	10,0 mm
d2	10,5 mm
İç çap d	4,50 mm
Yay stroku Z	9,0 mm
Çap Ds	20,0 mm
Yükseklik H3	9,00 mm
Çap Dmax(S)	21,0 mm

Not: DIN ISO 3302-1 M3 uyarınca elastomer parçalar için kabul edilebilir boyut toleransları



Art.-Nr.: 10.01.06.04149

**Teknik veriler**

Meme ucu ailesi	N 016
Vantuz malzemesi	Silikon SI-HD
Malzeme sertliği [Shore A]	65,0 Shore A
İş parçası yarıçapı dak (dışbükey)	30,0 mm
Boyut	20,00
Körük Sayısı	2,5

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Sipariş Verisi Aksesuarlar 10.01.06.04149**

Typ		Ürün numarası
Vantuz bağlantı nipeli	SA-NIP N016 G1/8-AG DN310	10.01.06.04062
Vantuz bağlantı nipeli	SA-NIP N016 M5-AG DN250	10.01.06.04365
Vantuz bağlantı nipeli	SA-NIP N016 M5-IG DN310	10.01.06.04689
Vantuz bağlantı nipeli	SA-NIP N016 G1/8-IG DN310	10.01.06.04690

