


SPB2f 25 SI-55 SC040

Teknik veriler

Attribute	Value
Vantuz malzemesi	Silikon SI
Malzeme sertliği [Shore A]	55.0 Shore A
Boyut	25.00
Körük Sayısı	2.5
Malzeme özellikleri	FDA uyumlu



Tasarım verileri SPB2f 25 SI-55 SC040

Tasarım verileri

Attribute	Value
Yükseklik H2	4.70 mm
Yükseklik H	25.30 mm
Dış çap D1	18.5 mm
Kafa çapı Dk	14.5 mm
İç çap d1	10.5 mm
d2	8.0 mm
İç çap d	7.50 mm
Yay stroku Z	9.8 mm
Çap Ds	25.0 mm
Yükseklik H3	6.70 mm

Art.-Nr.: 10.01.06.04226



Teknik veriler

Attribute	Value
Meme ucu ailesi	SC 040
Vantuz malzemesi	Silikon SI
Malzeme sertliği [Shore A]	55.0 Shore A
Emme kuvveti (-600mbar)	3.00 N
Ağırlık	2.8 g
Cilt	2.935 cm ³
Boyut	25.00
Körük Sayısı	2.5
400 mbar'da emme kuvveti	2.00 N
200 mbar'da emme kuvveti	1.00 N
Ürün ailesi	SPB2f

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.04226



Veri aksesuarları sipariş edin 10.01.06.04226

Typ	Ürün numarası
Schmalz-Konnektör SC 040 G1/8-AG	10.01.06.02490
Schmalz-Konnektör SC 040 G1/8-IG	10.01.06.02482

