

Körüklü vantuz (yuvarlak)


FGA 14 NBR-ESD-55 N062



Art.-Nr.: 10.01.06.04257



FGA 14 NBR-ESD-55 N062



Tasarım verileri FGA 14 NBR-ESD-55 N062

Teknik veriler

Vantuz malzemesi	Nitril kauçuk NBR-ESD
Malzeme sertliği [Shore A]	55,0 Shore A
Boyut	14,00
Körük Sayısı	1,5

Tasarım verileri

Yükseklik H2	3,80 mm
Yükseklik H	15,50 mm
Dış çap D1	13,7 mm
Kafa çapı Dk	10,0 mm
d2	5,0 mm
İç çap d	4,50 mm
Yay stroku Z	5,0 mm
Çap Ds	12,5 mm
Yükseklik H3	8,50 mm
Çap Dmax(S)	14,5 mm

Not: DIN ISO 3302-1 M3 uyarınca elastomer parçalar için kabul edilebilir boyut toleransları



WWW.SCHMALZ.COM/10.01.06.04257

Körüklü vantuz (yuvarlak)

FGA 14 NBR-ESD-55 N062



Art.-Nr.: 10.01.06.04257



Teknik veriler

Vantuz malzemesi	Nitril kauçuk NBR-ESD
İş parçası yarıçapı dak (dışbükey)	12,5 mm
Emme kuvveti (-600mbar)	1,20 N
Ağırlık	1,10 g
Boyut	14,00
Körük Sayısı	1,5
Ürün ailesi	FGA

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Sipariş Verisi Aksesuarlar 10.01.06.04257

Typ		Ürün numarası
Vantuz bağlantı nipel	SA-NIP N062 M5-AG DN250	10.01.06.05668
Vantuz bağlantı nipel	SA-NIP N062 G1/8-IG DN350	10.01.06.05669
Vantuz bağlantı nipel	SA-NIP N062 G1/8-AG DN350	10.01.06.05670



WWW.SCHMALZ.COM/10.01.06.04257