


Art.-Nr.: 10.01.06.04288



SC 030 G1/8-AG

## Technical data

| Attribute           | Value   |
|---------------------|---------|
| Connection type     | 030     |
| Nominal diameter dn | 3.10 mm |
| Fitting length      | 6.00 mm |
| Vacuum connection   | G1/8"-M |



Design data SC 030 G1/8-AG

## Design data

| Attribute           | Value    |
|---------------------|----------|
| Length L1           | 19.30 mm |
| Length L2           | 4.30 mm  |
| Length L            | 6.00 mm  |
| Outside diameter D2 | 5.8 mm   |
| Outside diameter D  | 7.20 mm  |
| Nominal diameter dn | 3.10 mm  |
| Thread G1           | G1/8"-M  |
| Thread length LG1   | 7.5 mm   |
| Key width SW1       | 14.0 mm  |
| Length L3           | 1.50 mm  |



## Technical data

| Attribute       | Value    |
|-----------------|----------|
| Material        | Aluminum |
| Connection type | 030      |



Schmalz-Connector

## SC 030 G1/8-AG



Art.-Nr.: 10.01.06.04288



### Further documentation

CAD data and other documents relating to the article can be found at: [www.schmalz.com/10.01.06.04288](http://www.schmalz.com/10.01.06.04288)



[WWW.SCHMALZ.COM/10.01.06.04288](http://WWW.SCHMALZ.COM/10.01.06.04288)