


Bellows suction cups (round)

SPB2f 25 SI-55 G1/8-AG



Art.-Nr.: 10.01.06.04316



SPB2f 25 SI-55 G1/8-AG

Suction cup SPB2f (elastomer part + connection element) is delivered assembled. The assembly consists of:

- Suction cup of type SPB2f - elastomer part, available in various diameters
- Connection element of type SC - available with various threads


Available spare parts: suction cup SPB2f, Schmalz-Connector

Technical data

Attribute	Value
Suction cup material	Silicone SI
Material hardness [Shore A]	55.0 Shore A
Size	25.00
Number of folds	2.5
Thread G1	G1/8"-M

Design data

Attribute	Value
Height H	31.30 mm
Nominal diameter dn	4.10 mm
d2	8.0 mm
Thread G1	G1/8"-M
Thread length LG1	7.5 mm
Key width SW1	14.0 mm
Spring stroke Z	9.8 mm
Diameter Ds	25.0 mm
Diameter Dmax(S)	28.0 mm



Design data SPB2f 25 SI-55 G1/8-AG



WWW.SCHMALZ.COM/10.01.06.04316

Bellows suction cups (round)

SPB2f 25 SI-55 G1/8-AG



Art.-Nr.: 10.01.06.04316



Technical data

Attribute	Value
Suction cup material	Silicone SI
Material hardness [Shore A]	55.0 Shore A
Suction force (-600mbar)	3.00 N
Weight	7.1 g
Volume	2.935 cm ³
Size	25.00
Number of folds	2.5
Suction force at -400 mbar	2.00 N
Suction force at -200 mbar	1.00 N
Product family	SPB2f

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.04316



Ordering Data Spare Parts 10.01.06.04316

Typ		Item number
Schmalz-Connector	SC 040 G1/8-AG	10.01.06.02490



Ordering Data Wear Parts 10.01.06.04316

Typ		Item number
Bellows suction cup (round)	SPB2f 25 SI-55 SC040	10.01.06.04226



WWW.SCHMALZ.COM/10.01.06.04316