


Körüklü vantuz (yuvarlak)

SFB1 40 SI-55 SC050


Art.-Nr.: 10.01.06.04372



Teknik veriler

Attribute	Value
Vantuz malzemesi	Silikon SI
Malzeme sertliği [Shore A]	55.0 Shore A
Boyut	40.00
Körük Sayısı	1.5

SFB1 40 SI-55 SC050



Tasarım verileri

Attribute	Value
Yükseklik H2	6.60 mm
Yükseklik H	29.70 mm
Dış çap D1	29.8 mm
Kafa çapı Dk	20.0 mm
İç çap d1	17.0 mm
d2	13.7 mm
İç çap d	11.40 mm
Yay stroku Z	10.0 mm
Çap Ds	40.0 mm
Çap Dmax(S)	42.0 mm

Tasarım verileri SFB1 40 SI-55 SC050



WWW.SCHMALZ.COM/10.01.06.04372

Art.-Nr.: 10.01.06.04372

**Teknik veriler**

Attribute	Value
Meme ucu ailesi	SC 050
Vantuz malzemesi	Silikon SI
Malzeme sertliği [Shore A]	55.0 Shore A
İş parçası yarıçapı dak (dışbükey)	30.0 mm
Çekme kuvveti	39.90 N
Emme kuvveti (-600mbar)	8.80 N
Ağırlık	7.5 g
Cilt	7.533 cm ³
Boyut	40.00
Körük Sayısı	1.5
Ürün ailesi	SFB1

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.04372

**Veri aksesuarları sipariş edin 10.01.06.04372**

Typ	Ürün numarası
Schmalz-Konnektör	SC 050 G1/4-AG SW410
Schmalz-Konnektör	SC 050 G1/4-IG SW410

WWW.SCHMALZ.COM/10.01.06.04372