




Технические данные

Attribute	Value
Материал присоски	EPDM
Твердость материала [Shore A]	45,0 Shore A
размер	10,00
Количество складок	1,5

SFB1 10 EPDM-45 SC030



Конструктивные данные

Attribute	Value
Высота H2	4,20 mm
Высота H	12,30 mm
Наружный диаметр D1	8,2 mm
Диаметр головки Dk	8,7 mm
Внутренний диаметр d1	7,3 mm
d2	3,4 mm
Внутренний диаметр d	5,50 mm
Ход пружины Z	2,5 mm
Диаметр Ds	10,0 mm
Диаметр Dmax(S)	11,0 mm

Конструктивные данные SFB1 10 EPDM-45 SC030



Art.-Nr.: 10.01.06.04373



Технические данные

Attribute	Value
Семейство ниппелей	SC 030
Материал присоски	EPDM
Твердость материала [Shore A]	45,0 Shore A
Радиус заготовки мин. (выпуклый)	10,0 mm
Сила отрыва	2,70 N
Всасывающая сила (-600 мбар)	0,50 N
Объем	0,287 cm ³
размер	10,00
Количество складок	1,5
Семейство продуктов	SFB1

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.04373



Данные для заказа Аксессуары 10.01.06.04373

Тип	Количество предметов
Соединитель Schmalz SC 030 M5-AG	10.01.06.02802

