


SFB1 15 EPDM-45 SC040

Teknik veriler

Attribute	Value
Vantuz malzemesi	EPDM
Malzeme sertliği [Shore A]	45,0 Shore A
Boyut	15,00
Körük Sayısı	1,5

Tasarım verileri

Attribute	Value
Yükseklik H2	4,70 mm
Yükseklik H	16,00 mm
Dış çap D1	11,5 mm
Kafa çapı Dk	12,8 mm
İç çap d1	10,4 mm
d2	4,7 mm
İç çap d	7,50 mm
Yay stroku Z	4,0 mm
Çap Ds	15,0 mm
Çap Dmax(S)	16,0 mm



Tasarım verileri SFB1 15 EPDM-45 SC040

Art.-Nr.: 10.01.06.04374

**Teknik veriler**

Attribute	Value
Meme ucu ailesi	SC 040
Vantuz malzemesi	EPDM
Malzeme sertliği [Shore A]	45,0 Shore A
İş parçası yarıçapı dak (dışbükey)	12,0 mm
Çekme kuvveti	6,10 N
Emme kuvveti (-600mbar)	1,00 N
Cilt	0,759 cm ³
Boyut	15,00
Körük Sayısı	1,5
Ürün ailesi	SFB1

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.04374

**Sipariş Verisi Aksesuarlar 10.01.06.04374**

Typ	Ürün numarası
Schmalz-Konnektör	SC 040 M5-AG
Schmalz-Konnektör	SC 040 G1/8-AG
Schmalz-Konnektör	SC 040 G1/8-IG

