


SFB1 40 EPDM-45 SC050

Teknik veriler

Attribute	Value
Vantuz malzemesi	EPDM
Malzeme sertliği [Shore A]	45,0 Shore A
Boyut	40,00
Körük Sayısı	1,5

Tasarım verileri

Attribute	Value
Yükseklik H2	6,60 mm
Yükseklik H	29,70 mm
Dış çap D1	29,8 mm
Kafa çapı Dk	20,0 mm
İç çap d1	17,0 mm
d2	13,7 mm
İç çap d	11,40 mm
Yay stroku Z	10,0 mm
Çap Ds	40,0 mm
Çap Dmax(S)	42,0 mm



Tasarım verileri SFB1 40 EPDM-45 SC050

Art.-Nr.: 10.01.06.04378

**Teknik veriler**

Attribute	Value
Meme ucu ailesi	SC 050
Vantuz malzemesi	EPDM
Malzeme sertliği [Shore A]	45,0 Shore A
İş parçası yarıçapı dak (dışbükey)	30,0 mm
Çekme kuvveti	39,90 N
Emme kuvveti (-600mbar)	8,80 N
Cilt	7,533 cm ³
Boyut	40,00
Körük Sayısı	1,5
Ürün ailesi	SFB1

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.04378

**Sipariş Verisi Aksesuarlar 10.01.06.04378**

Typ	Ürün numarası
Schmalz-Konnektör SC 050 G1/4-AG SW410	10.01.06.04347
Schmalz-Konnektör SC 050 G1/4-IG SW410	10.01.06.04348

WWW.SCHMALZ.COM/10.01.06.04378