


Körüklü vantuz (yuvarlak)

SFB1 10 HT1-60 SC030



Art.-Nr.: 10.01.06.04379




SFB1 10 HT1-60 SC030

Teknik veriler

Attribute	Value
Vantuz malzemesi	Yüksek sıcaklık malzemesi HT1
Malzeme sertliği [Shore A]	60.0 Shore A
Boyut	10.00
Körük Sayısı	1.5

Tasarım verileri

Attribute	Value
Yükseklik H2	4.20 mm
Yükseklik H	12.30 mm
Dış çap D1	8.2 mm
Kafa çapı Dk	8.7 mm
İç çap d1	7.3 mm
d2	3.4 mm
İç çap d	5.50 mm
Yay stroku Z	2.5 mm
Çap Ds	10.0 mm
Çap Dmax(S)	11.0 mm



Tasarım verileri SFB1 10 HT1-60 SC030



WWW.SCHMALZ.COM/10.01.06.04379

Art.-Nr.: 10.01.06.04379

**Teknik veriler**

Attribute	Value
Meme ucu ailesi	SC 030
Vantuz malzemesi	Yüksek sıcaklık malzemesi HT1
Malzeme sertliği [Shore A]	60.0 Shore A
İş parçası yarıçapı dak (dışbükey)	10.0 mm
Çekme kuvveti	2.70 N
Emme kuvveti (-600mbar)	0.50 N
Cilt	0.287 cm ³
Boyut	10.00
Körük Sayısı	1.5
Ürün ailesi	SFB1

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.04379

**Veri aksesuarları sipariş edin 10.01.06.04379**

Typ	Ürün numarası
Schmalz-Konnektör	SC 030 M5-AG
	10.01.06.02802

