




Teknik veriler

Vantuz malzemesi	EPDM
Malzeme sertliği [Shore A]	45,0 Shore A
Boyut	20,00

SFB1 20 EPDM-45 G1/8-IG

Vantuz SFF / SFB1 (elastomer parça + bağlantı nipeli) monte edilmiş olarak teslim edilir.

Mevcut yedek parçalar: vantuz SFF / SFB1, bağlantı nipeli SC



Tasarım verileri

Yükseklik H	31,50 mm
Nominal çap dn	4,10 mm
d2	6,6 mm
Diş uzunluğu LG1	8,0 mm
Anahtar boyutu SW1	14,0 mm
Yay stroku Z	5,0 mm
Çap Ds	20,0 mm
Çap Dmax(S)	21,0 mm
Diş G1	G1/8-IG

Tasarım verileri SFB1 20 EPDM-45 G1/8-IG

Körüklü vantuzlar (yuvarlak)

SFB1 20 EPDM-45 G1/8-IG



Art.-Nr.: 10.01.06.04407



Teknik veriler

Vantuz malzemesi	EPDM
Malzeme sertliđi [Shore A]	45,0 Shore A
Çekme kuvveti	10,50 N
Emme kuvveti (-600mbar)	2,10 N
Cilt	1,200 cm ³
Boyut	20,00
Körük Sayısı	1,5
Ürün ailesi	SFB1

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Sipariş Verisi Yedek Parça 10.01.06.04407

Typ		Ürün numarası
Körüklü vantuz (yuvarlak)	SFB1 20 EPDM-45 SC040	10.01.06.04375
Schmalz-Konnektör	SC 040 G1/8-IG	10.01.06.02482



WWW.SCHMALZ.COM/10.01.06.04407