

Art.-Nr.: 10.01.06.04410




Teknik veriler

Attribute	Value
Vantuz malzemesi	EPDM
Malzeme sertliği [Shore A]	45.0 Shore A
Boyut	25.00

SFB1 25 EPDM-45 G1/8-AG

Vantuz SFF / SFB1 (elastomer parça + bağlantı nipeli) monte edilmiş olarak teslim edilir.

Mevcut yedek parçalar: vantuz SFF / SFB1, bağlantı nipeli SC



Tasarım verileri

Attribute	Value
Yükseklik H	25.20 mm
Nominal çap dn	4.10 mm
d2	8.2 mm
Diş uzunluğu LG1	7.5 mm
Anahtar boyutu SW1	14.0 mm
Yay stroku Z	6.5 mm
Çap Ds	25.0 mm
Çap Dmax(S)	26.5 mm
Diş G1	G1/8-AG

Tasarım verileri SFB1 25 EPDM-45 G1/8-AG



Art.-Nr.: 10.01.06.04410

**Teknik veriler**

Attribute	Value
Vantuz malzemesi	EPDM
Malzeme sertliği [Shore A]	45.0 Shore A
Çekme kuvveti	18.50 N
Emme kuvveti (-600mbar)	3.20 N
Cilt	1.900 cm ³
Boyut	25.00
Körük Sayısı	1.5
Ürün ailesi	SFB1

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.04410

**Yedek parçalar için sipariş verileri 10.01.06.04410**

Typ	Ürün numarası
Körüklü vantuz (yuvarlak)	SFB1 25 EPDM-45 SC040 10.01.06.04376
Schmalz-Konnektör	SC 040 G1/8-AG 10.01.06.02490

