


Körüklü vantuzlar (yuvarlak)
SFB1 25 HT1-60 G1/8-IG




Art.-Nr.: 10.01.06.04414



SFB1 25 HT1-60 G1/8-IG

Vantuz SFF / SFB1 (elastomer parça + bağlantı nipeli) monte edilmiş olarak teslim edilir.

Mevcut yedek parçalar: vantuz SFF / SFB1, bağlantı nipeli SC



Tasarım verileri SFB1 25 HT1-60 G1/8-IG

Teknik veriler

Vantuz malzemesi	Yüksek sıcaklık malzemesi HT1
Malzeme sertliği [Shore A]	60,0 Shore A
Boyut	25,00

Tasarım verileri

Yükseklik H	33,20 mm
Nominal çap dn	4,10 mm
d2	8,2 mm
Diş uzunluğu LG1	8,0 mm
Anahtar boyutu SW1	14,0 mm
Yay stroku Z	6,5 mm
Çap Ds	25,0 mm
Çap Dmax(S)	26,5 mm
Diş G1	G1/8-IG



WWW.SCHMALZ.COM/10.01.06.04414

Körüklü vantuzlar (yuvarlak)
SFB1 25 HT1-60 G1/8-IG



Art.-Nr.: 10.01.06.04414



Teknik veriler

Vantuz malzemesi	Yüksek sıcaklık malzemesi HT1
Malzeme sertliği [Shore A]	60,0 Shore A
Çekme kuvveti	18,50 N
Emme kuvveti (-600mbar)	3,20 N
Cilt	1,900 cm ³
Boyut	25,00
Körük Sayısı	1,5
Ürün ailesi	SFB1

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Sipariş Verisi Yedek Parça 10.01.06.04414

Typ	Ürün numarası
Körüklü vantuz (yuvarlak)	SFB1 25 HT1-60 SC040 10.01.06.04382
Schmalz-Konnektör	SC 040 G1/8-IG 10.01.06.02482



WWW.SCHMALZ.COM/10.01.06.04414