

Art.-Nr.: 10.01.06.04419




Teknik veriler

Attribute	Value
Vantuz malzemesi	EPDM
Malzeme sertliği [Shore A]	45,0 Shore A
Boyut	30,00

SFB1 30 EPDM-45 G1/4-IG

Vantuz SFB1 (elastomer parça + bağlantı nipeli) monte edilmiş olarak teslim edilir.

Mevcut yedek parçalar: vantuz SFB1, bağlantı nipeli SC



Tasarım verileri

Attribute	Value
Yükseklik H	37,70 mm
Nominal çap dn	4,10 mm
d2	9,9 mm
Diş uzunluğu LG1	12,0 mm
Anahtar boyutu SW1	17,0 mm
Yay stroku Z	8,0 mm
Çap Ds	30,0 mm
Çap Dmax(S)	31,5 mm
Diş G1	G1/4-IG

Tasarım verileri SFB1 30 EPDM-45 G1/4-IG



Art.-Nr.: 10.01.06.04419

**Teknik veriler**

Attribute	Value
Vantuz malzemesi	EPDM
Malzeme sertliği [Shore A]	45,0 Shore A
Çekme kuvveti	23,70 N
Emme kuvveti (-600mbar)	4,60 N
Cilt	2,900 cm ³
Boyut	30,00
Körük Sayısı	1,5
Ürün ailesi	SFB1

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.04419

**Sipariş Verisi Yedek Parça 10.01.06.04419**

Typ	Ürün numarası
Körüklü vantuz (yuvarlak)	SFB1 30 EPDM-45 SC040 10.01.06.04377
Schmalz-Konnektör	SC 040 G1/4-IG 10.01.06.02918

