


Art.-Nr.: 10.01.06.04425



SFB1 40 EPDM-45 G1/4-IG

Vantuz SFF / SFB1 (elastomer parça + bağlantı nipel) monte edilmiş olarak teslim edilir.

Mevcut yedek parçalar: vantuz SFF / SFB1, bağlantı nipel SC



Tasarım verileri SFB1 40 EPDM-45 G1/4-IG

## Teknik veriler

| Attribute                  | Value        |
|----------------------------|--------------|
| Vantuz malzemesi           | EPDM         |
| Malzeme sertliği [Shore A] | 45,0 Shore A |
| Boyut                      | 40,00        |

## Tasarım verileri

| Attribute          | Value    |
|--------------------|----------|
| Yükseklik H        | 46,90 mm |
| Nominal çap dn     | 4,10 mm  |
| d2                 | 13,7 mm  |
| Diş uzunluğu LG1   | 12,0 mm  |
| Anahtar boyutu SW1 | 17,0 mm  |
| Yay stroku Z       | 10,0 mm  |
| Çap Ds             | 40,0 mm  |
| Çap Dmax(S)        | 42,0 mm  |
| Diş G1             | G1/4-IG  |



Art.-Nr.: 10.01.06.04425

**Teknik veriler**

| Attribute                  | Value                 |
|----------------------------|-----------------------|
| Vantuz malzemesi           | EPDM                  |
| Malzeme sertliği [Shore A] | 45,0 Shore A          |
| Çekme kuvveti              | 39,90 N               |
| Emme kuvveti (-600mbar)    | 8,80 N                |
| Cilt                       | 7,500 cm <sup>3</sup> |
| Boyut                      | 40,00                 |
| Körük Sayısı               | 1,5                   |
| Ürün ailesi                | SFB1                  |

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: [www.schmalz.com/10.01.06.04425](http://www.schmalz.com/10.01.06.04425)

**Sipariş Verisi Yedek Parça 10.01.06.04425**

| Typ                       | Ürün numarası                        |
|---------------------------|--------------------------------------|
| Körüklü vantuz (yuvarlak) | SFB1 40 EPDM-45 SC050 10.01.06.04378 |
| Schmalz-Konnektör         | SC 050 G1/4-IG SW410 10.01.06.04348  |

